




XKB Product features

- Voltage: < 12V
- Current: < 20mA
- Conduction time: 2ms
- Closed circuit resistance: < 30ohm
- Open circuit resistance: > 10m ohm
- High temperature resistance: 120 degrees
- Terminal tension: 500gf / min
- Humidity: 95RH40 ° 96 hours
- Operating life: 200000 times

XKB Product features:

产品特性:

1. Sw-18150p is a sealed spring type non directional vibration inductive trigger switch, which can be triggered at any angle.XKB
- 1.SW-18150P为密封式弹簧型无方向性振动感应触发开关, 任何角度均可触发。
2. This series of switches are in open circuit off state when they are at rest. When they are touched by external force and reach the corresponding vibration force, or when the moving speed reaches the appropriate (eccentric) centrifugal force, the conductive contact feet will produce instantaneous conduction and present on state. When the external force disappears, the switch will return to open circuit off state.XKB
- 2.本系列开关在静止时为开路OFF状态, 当受到外力碰触而达到相应震动力时, 或移动速度达到适当(偏)离心力时, 导电接触脚会产生瞬间导通而呈ON状态, 当外力消失时, 开关恢复为开路OFF状态。
3. This series of switches with model P are completely sealed and can be waterproof and dustproof.XKB
- 3.本系列开关带P型号的, 为完全密封式封装, 可防水防尘。
4. The trigger sensitivity of this series of switches is high sensitive.
- 4.本系列开关触发灵敏度为高灵敏。
5. The service life of this series of switches can reach 200000 times under normal use.
- 5.本系列开关在正常使用情况下寿命可达200,000次。
6. This series of switches are suitable for triggering small current circuit.
- 6.本系列开关适用于小电流电路的触发。
7. All materials of this series of switches are made of environmental protection RoHS materials.XKB
- 7.本系列开关所有材质均采用环保ROHS材质制造。



⑤	Housing and cover	1	PET heat shrinkable tubes	
④	Sealing glue	1	ROSH epoxy resin	
③	Spring C	1	SUS	0.1
②	Pin B	1	Brass	Gold plating
①	Tube A	1	PC	Black
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

广东星坤科技股份有限公司

生	日期	units:	mm
Δx		tolerance:	
Δx		X.X	±0.2mm
Δx		X.XX	±0.1mm
MARK	DESCRIPTION	X.XXX	±0.05mm
文件	工程	UNSPECIFIED TOLERANCES	
章	REVISIONS		
	DATE	REVISED	APPROVED
	www.xk-dg.cn	www.helloxkb.com	www.helloxkb.cn

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	Vibration switch
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			SW-18015PZR-10G12S1
WEIGHT	SHEET	REVISION	
1.0g	1/1	A0	