


Specifications:

- 规格:
- Voltage rating:250VAC/DC
额定电压: 250V AC/DC
 - Current rating:3A AC/DC
额定电流: 3A AC/DC
 - Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
 - Temperature range: -55°C~+105°C
温度范围: -55°C~+105°C
 - Insulation resistance:1000MΩ MIN
绝缘电阻:1000MΩ MIN
 - Contact resistance:30mΩ Max
接触电阻: 30mΩ Max
- Material:
- 材料:
- Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
 - The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC-SD,镀镍/镀锡/镀金
 - Terminal:Copper alloy
端子: 铜合金

X01 XX W X X X X
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09;15;25;37
- ③ Welding Board Angle :W-Male
- ④ T: Tradutional C: Car-pin
- ⑤ Plating Catogoty: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn
- ⑥ Color:B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4

| NUMBER OF POSITIONS | DIMENSION | | | |
|---------------------|-----------|--------|--------|--------|
| | A±0.25 | B±0.13 | C±0.38 | D±0.25 |
| 9 | 18.00 | 24.99 | 30.80 | 19.28 |
| 15 | 26.50 | 33.32 | 39.20 | 27.51 |
| 25 | 40.00 | 47.04 | 53.05 | 41.28 |
| 37 | 56.60 | 63.50 | 69.40 | 57.71 |



广东星坤科技股份有限公司

| | |
|-------|----|
| 姓名 | 日期 |
| 修改 | 日期 |
| 文件工程章 | |

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | ANGLAR | ±5° |
|-----------|-------------|------|---------|----------|-------------|------------------------|
| | | | | | L ≤ 4 | ±0.2 |
| | | | | | 4 < L ≤ 16 | ±0.3 |
| | | | | | 16 < L ≤ 63 | ±0.4 |
| | | | | | L > 63 | ±0.5 |
| REVISIONS | | | | | | UNSPECIFIED TOLERANCES |



| | | |
|--------------------------------------|-------------|-----------------------|
| DSND | SCALE: N/A | MODEL TYPE: D-SUB |
| DWN | VIEW: | PART NO.: X01XXWXXXX |
| CHKD | UNIT: mm/in | DWG NO.: X-X01XXWXXXX |
| APPD | SIZE: A4 | WEIGHT SHEET REVISION |
| XKB INDUSTRIAL PRECISION CO.,LIMITED | | 1/1 A0 |