

Specifications:


规格:

- 1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
 - 2.Current rating:3A AC/DC
额定电流: 3A AC/DC
 - 3.Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
 - 4.Temperature range: -55℃~+105℃
温度范围: -55℃~+105℃
 - 5.Insulation resistance:1000MΩ MIN
绝缘电阻: 1000MΩ MIN
 - 6.Contact resistance:30mΩ Max
接触电阻: 30mΩ Max
- Material:
材料:
- 7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
 - 8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC-SD, 镀镍/镀锡/镀金
 - 9.Terminal:Copper alloy
端子: 铜合金

X01 XX F X X X X
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09:15;25;37
- ③ Welding Board Angle :F-Female
- ④ T: Traditional C: Car-pin
- ⑤ Planting Category: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn
- ⑥ Color:B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	16.35	24.99	30.80	19.28
15	24.75	33.30	39.20	27.65
25	38.35	47.04	53.05	41.28
37	54.75	63.50	69.40	57.71



广东星坤科技股份有限公司

审核	日期
生效	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5



DSND	SCALE: N/A	MODEL TYPE: D-SUB
DWN	VIEW:	PART NO.: X01XXFXXXX
CHKD	UNIT: mm/in	DWG NO.: X-X01XXFXXXX
APPD	SIZE: A4	WEIGHT
		SHEET 1/1
		REVISIT A0

XKB INDUSTRIAL PRECISION CO., LIMITED