



Main

Range of Product	Harmony 9001KY
Product or Component Type	Control station
Device short name	9001KY
Provided equipment	Label plate START-STOP
Contact block name	KA51
Product Specific Application	For hoisting and mechanical handling applications
Level or class	Class II Division 2 Group G Class III

Complementary

Enclosure/cubicle description	Wall-mounted enclosure 2 cut-outs Ø 30 mm
Enclosure material	Polymeric
Type of Installation	Indoor/outdoor
Control station composition	2 push-buttons 2 NO + 2 NC
Mechanical interlocking	Without mechanical interlock
Connector Type	Screw clamp connector
Connections - terminals	Direct connection AWG 2) solid stranded Direct connection AWG 12) solid stranded Direct connection AWG 24) solid stranded
[Ue] rated operational voltage	115 V 240 V
[Ie] rated operational current AC	3 A

Environment

NEMA Degree of Protection	NEMA 13 NEMA 1 NEMA 3 NEMA 4
Environmental characteristic	Resistant against immersion in water Dust and oil resistant
Product Certifications	UL Listed
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
GTIN	785901126331
Nbr. of units in pkg.	1
Package weight(Lbs)	32.00 oz (907.185 g)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.16 in (25.806 cm)
Package 1 width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------