

Product specifications

Eaton KU12-WNUV

Catalog Number: KU12-WNUV

Eaton Bussmann KU series panel mount terminal block connector, 600 V, 60 A, 12-pole, Black, Molded nuclear grade noryl base, Nickel-plated brass washer head

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Bussmann KU series panel mount terminal block connector	KU12-WNUV
Product Length/Depth	Product Height
8.75 in	1.25 in
Product Width	Product Weight
2 in	0.4 lb
Warranty	Compliances
Not Applicable	RoHS Compliant
Certifications	
Contact Manufacturer	

Electrical ratings

Amperage Rating

60A

Voltage rating

600 V

Physical details

Number Of Poles

Twelve-pole

Resources

Catalogs

KU12-WNUV~TERM BLK. MARKED VERTICAL

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)