

### Main

Device short name	A
Enclosure type	Standard environment enclosure indoor
Product Specific Application	Mechanically alternating the operation of two pumps or motors
Switch application	Standard

### Complementary

Electrical Connection	Screw clamp terminal
Material	Stainless steel: float/rod Nitrile (Buna-N): seal ring
Maximum Horse Power Rating	3 Hp 115 V AC, 3 phase 2 Hp 115 V AC, 1 phase 3 Hp 230 V AC, 1 phase 5 Hp 230 V AC, 3 phase 1 hp 460/575 V AC, 3 phase
Mounting Support	Flange
Number of poles	2
Permissible voltage	575 V AC
Switch Function	DPST

### Environment

NEMA Degree of Protection	NEMA 1
---------------------------	--------

### Ordering and shipping details

Category	US1CP7G21601
Discount Schedule	CP7G
GTIN	785901591047
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.76 in (29.871 cm)
Package 1 Width	4.63 in (11.76 cm)
Package 1 Length	29.87 in (75.872 cm)
Package 1 Weight	4.49 lb(US) (2.037 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------