

Schottky Barrier Rectifier

SS28A - SS210A

Features

- Metal silicon junction, majority carrier conduction
- High forward surge current capability
- Low forward voltage drop
- High temperature soldering guaranteed: 260°C @ 10s
- Robust guarding for over voltage protection
- RoHS compliant with Halogen-free



Mechanical Data

- Case: SMA molded plastic
- Molding compound: UL flammability classification rating 94V-0
- Terminals: Matte tin plated leads; solderable per J-STD-002 and JESD22-B102
- Polarity: Color band denotes cathode end

Maximum Ratings (@ T_A = 25°C unless otherwise specified)

Parameter	Symbol	SS28A	SS29A	SS210A	Unit
Peak Repetitive Reverse Voltage	V _{RRM}	80	90	100	V
RMS Reverse Voltage	V _{RMS}	56	63	70	V
DC Blocking Voltage	V _{DC}	80	90	100	V
Maximum Average Forward Output Current	I _{F_AV}	2.0			A
Peak Forward Surge Current, 8.3ms Single Half Sine wave	I _{FSM}	50			A

Thermal Characteristics

Parameter	Symbol	SS28A	SS29A	SS210A	Unit
Typical Thermal Resistance *1	R _{θJA}	70			°C/W
	R _{θJC}	25			
	R _{θJL}	30			
Operating Junction Temperature Range	T _J	-55 ~ +150			°C
Storage Temperature Range	T _{STG}	-55 ~ +150			°C

Note *1: Device mounted on p.c.b. with 10 mm x 20 mm x 0.1 mm copper pad area

Schottky Barrier Rectifier

SS28A - SS210A

Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions		Typ.	Max.	Unit
Instantaneous Forward Voltage ^{*1}	V_F	$I_F = 2.0\text{A}$	@ $T_A = 25^\circ\text{C}$	-	0.80	V
Reverse Current ^{*2}	I_R	Rated V_R	@ $T_J = 25^\circ\text{C}$	-	30	μA
			@ $T_J = 100^\circ\text{C}$	-	5	mA

Note^{*1}: Pulse test: 300us pulse width, 1 % duty cycle

Note^{*2}: Pulse test: Pulse width 40ms

Schottky Barrier Rectifier

SS28A - SS210A

Ratings and Characteristic Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Surge Current Derating Curve




Fig.3 Typical Forward Voltage Characteristics






Fig.4 Typical Reverse Characteristics




Schottky Barrier Rectifier

SS28A - SS210A

Package Outline Dimensions (Unit: mm)



Mounting Pad Layout (Unit: mm)



Ordering Information

Part Number	Marking	Package	Shipping Quantity
SS28A	SS28A	SMA	5000 / Tape & Reel
SS29A	SS29A	SMA	5000 / Tape & Reel
SS210A	SS210A	SMA	5000 / Tape & Reel