






POLES	P/N	A	B
2	1.5T-2P-WV	1.50	6.00
3	1.5T-3P-WV	3.00	7.50
4	1.5T-4P-WV	4.50	9.00
5	1.5T-5P-WV	6.00	10.50
6	1.5T-6P-WV	7.50	12.00
7	1.5T-7P-WV	9.00	13.50
8	1.5T-8P-WV	10.50	15.00
9	1.5T-9P-WV	12.00	16.50
10	1.5T-10P-WV	13.50	18.00
11	1.5T-11P-WV	15.00	19.50
12	1.5T-12P-WV	16.50	21.00
13	1.5T-13P-WV	18.00	22.50
14	1.5T-14P-WV	19.50	24.00
15	1.5T-15P-WV	21.00	25.50
16	1.5T-16P-WV	22.50	27.00
17	1.5T-17P-WV	24.00	28.50
18	1.5T-18P-WV	25.50	30.00
19	1.5T-19P-WV	27.00	31.50
20	1.5T-20P-WV	28.50	33.00



With Cover

技术参数 (SPECIFICATIONS)

- ◆ 额定电压: 50V AC DC
Voltage rating: 50V AC DC
- ◆ 额定电流: 1.0A AC DC(28AWG)
Current rating: 1.0A AC DC(28AWG)
- ◆ 耐压值: 500V AC/minute
Withstand voltage 500V AC/minute
- ◆ 绝缘电阻: 100MΩ MIN.
Insulation resistance: 100MΩ MIN.
- ◆ 接触电阻: 20mΩ MAX.(初始值)
Contact resistance: 20mΩ MAX.(Initial)
- ◆ 工作温度: -25°C~+85°C
Working Temperature: -25°C~+85°C
- ◆ 间距: 1.5 mm
Pitch: 1.5mm

材料 (MATERIAL)

- ◆ 绝缘体: LCP UL94V-0
Insulator: LCP UL94V-0
- ◆ 焊片: 磷青铜镀锡
Solder tab: Phosphor bronze TIN-Plating
- ◆ 接触针: 磷青铜镀锡
Contact PIN: Phosphor bronze TIN-Plating

APPROVALS			DATE		 hro®		
DRAWN		LIUCAN	2023.11.3				
CHECKED				TITLE:		Bar Connector Series	
APPROVALS				PART NO.		1.5T-nP-WV	
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.		SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			