








- NOTES:(Unless otherwise specified)
1. Dimension shall be interpreted per ANSI Y14.5M.
 - 2.Current Rating:0.5 A Per pin.
 - 3.Voltage Rating: 50V AC/DC
 - 4.Working Temperature: -55°C to +125°C.



| Pin | A | B | C | D | E | F |
|---------|-------|-------|-------|-------|-------|-------|
| 10 Pin | 4.60 | 2.00 | 2.70 | 3.10 | 4.10 | 5.60 |
| 14 Pin | 5.60 | 3.00 | 3.70 | 4.10 | 5.10 | 6.60 |
| 20 Pin | 7.10 | 4.50 | 5.20 | 5.60 | 6.60 | 8.10 |
| 30 Pin | 9.60 | 7.00 | 7.70 | 8.10 | 9.10 | 10.60 |
| 32 Pin | 10.10 | 7.50 | 8.20 | 8.60 | 9.60 | 11.10 |
| 36 Pin | 11.10 | 8.50 | 9.20 | 9.60 | 10.60 | 12.10 |
| 40 Pin | 12.10 | 9.50 | 10.20 | 10.60 | 11.60 | 13.10 |
| 50 Pin | 14.60 | 12.00 | 12.70 | 13.10 | 14.10 | 15.60 |
| 60 Pin | 17.10 | 14.50 | 15.20 | 15.60 | 16.60 | 18.10 |
| 80 Pin | 22.10 | 19.50 | 20.20 | 20.60 | 21.60 | 23.10 |
| 100 Pin | 27.10 | 24.50 | 25.20 | 25.60 | 26.60 | 28.10 |



Ordering Information

HC-PBB12 ** (*) - NDS - 0.5V - P - 03

Type NB=母座 NC=母座 High (H) 台高 (3.0)~3.00mm No. of Pins 10~120Pin Nature DS=Female (母座) PITCH 0.5V=0.5mm Post (焊耳)

3.5/4.0/5.0mm

| | | |
|-----|-----------------|--|
| 3 | BRASS | 100u" MIN.TIN PLATED UNDER PLATING; 50u" NIKEL PLATED |
| 2 | PHOSPHOR BRONZE | CONTACT AREA: GOLD PALTED LEAD AREA: GOLD FLASH UNDER PLATING; 50u" NIKEL PLATED |
| 1 | POLYAMIDE | UL94V-0, BLACK/NATURE |
| NO. | MATERIAL | FINISH.REMARKS |

| GENERAL TOLERANCE | | 制图 DRAWING |
|-------------------|-------|---------------|
| DIM | TOL | 审核 CHECK |
| X.X | ±0.30 | 批准 APPROVAL |
| X.XX | ±0.20 | 比例 SCALE |
| X.XXX | ±0.10 | 投影 Projection |
| Angle | ±3.0° | |

深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO.,LTD

| | | | |
|---------------|------------------------|----------|-----|
| 产品名称 TITLE | BTB 0.5 立贴 母座 带焊耳 | 版本 REV. | A |
| 产品料号 PART NO. | HC-PBB12NB-NDS-0.5V-03 | 单位 UNITS | mm |
| 材料 MATERIAL | | 页次 SHEET | 1/1 |