





**Electrical properties**

1. Current rating: 7A AC\DC (AWG #26)
2. Voltage rating: 250V AC\DC
3. Temperature range: -25°C~+85°C
4. Contact resistance: Initial value/30Ωm max
5. Insulation resistance: 1000ΩMmin
6. Withstanding voltage: 1000V AC/ minute
7. Applicable wire: AWG #18 to #22

**Environmental controls**

1. Banned contains SS - 00259 are restricted substances.
2. The corresponding issued by SGS or ITS icp-aes data, Not the material in a list, and validity.

Pin	A	B	C
2	3.96	11.88	8.6
3	7.92	15.84	12.56
4	11.88	19.8	16.52
5	15.84	23.76	20.48
6	19.8	27.72	24.44
7	23.76	31.68	28.4
8	27.72	35.64	32.36
9	31.68	39.6	36.32
10	35.64	43.56	40.28

APPROVALS		DATE																
DRAWN	LIUCAN	2022.4.16				TITLE:	Bar Connector Series											
CHECKED			PART NO.	3.96T-nP-WV														
APPROVALS			TOLERANCES ARE	<table border="1"> <tr> <td>30~以上</td> <td>±0.30</td> <td rowspan="4">ANGLE</td> <td rowspan="4">UNIT: mm</td> <td rowspan="4">SCALE: 1:1</td> <td rowspan="4">PROJ: </td> </tr> <tr> <td>10~30</td> <td>±0.20</td> </tr> <tr> <td>5~10</td> <td>±0.15</td> </tr> <tr> <td>~ 5</td> <td>±0.10</td> </tr> </table>	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	10~30	±0.20	5~10	±0.15	~ 5	±0.10	DRAWING NO.	SHEET 1 OF 1
30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 													
10~30	±0.20																	
5~10	±0.15																	
~ 5	±0.10																	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			