

SEK mezz Fe 30P Press-in 4.5mm PL2




Image is for illustration purposes only. Please refer to product description.

Part number	09 19 530 6829
Specification	SEK mezz Fe 30P Press-in 4.5mm PL2
HARTING eCatalogue	https://b2b.harting.com/09195306829

Identification

Category	Connectors
Series	SEK Mezzanine
Element	Female connector
Description of the contact	Straight

Version

Termination method	Press-in termination
Connection type	PCB to PCB Motherboard to daughtercard
Number of contacts	30
Termination length	4.5 mm

Technical characteristics

Contact rows	2
Contact spacing (termination side)	2.54 mm
Rated current	1 A
Insulation resistance	$>10^9 \Omega$
Contact resistance	$\leq 20 \text{ m}\Omega$
Limiting temperature	-55 ... +125 °C
Insertion and withdrawal force	$\leq 60 \text{ N}$
Performance level	2
Mating cycles	≥ 250
Test voltage $U_{r.m.s.}$	1 kV



Pushing Performance
Since 1945

Technical characteristics

Isolation group	IIIa ($175 \leq \text{CTI} < 400$)
PCB thickness	1.6 mm +1.6

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Nickel plated Termination side Au over Pd/Ni Mating side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60603-13
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	100
Net weight	7.86 g
Country of origin	China
European customs tariff number	85366990
GTIN	5713140211117
ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)