

## HPP V4 Power crimp cont. female 1,5mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	09 46 500 0402
Specification	HPP V4 Power crimp cont. female 1,5mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/09465000402">https://b2b.harting.com/09465000402</a>

### Identification

Category	Contacts
Series	HARTING PushPull (V4)
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	1.5 mm <sup>2</sup>
Conductor cross-section	AWG 16 ... AWG 14
Mating cycles	≥750

### Material properties

Material (contacts)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead



Pushing Performance  
Since 1945

Material properties

ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel

Commercial data

Packaging size	100
Net weight	0.49 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140065451
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors