



Main

Range of Product	9080G
Product Type	Terminal block
Color	Natural

Complementary

Voltage Rating	600 V AC/DC
Current Rating	60 A UL 60 A CSA
Assemblies Consist of	10 terminal blocks 1 end barrier 2 end clamp(s) 1 mounting track
Wire Size	AWG 22...AWG 8 copper
Mounting Type	9080GH track
Certifications	UL recognized E60616 CCN XCFR2[RETURN]CSA file 62144 class 6228 01[RETURN]CE
Protection Type	Fingersafe DIN 57470
Ambient Air Temperature for Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Lug copper 18...20 lbf.in (2.03...2.26 N.m) : AWG 22...AWG 8 copper)
Height	1.82 in (46.23 mm)
Width	1.72 in (43.69 mm)
Depth	6 in (152.40 mm)

Ordering and shipping details

Category	21702-9080 G (NOT GCB)
Discount Schedule	CP5
GTIN	00785901768708
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
