




PCB LAYOUT
(TOP VIEW)

General Specification
Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
Operating Environment
Standard Temperature: -20℃~+70℃
Industrial Temperature: -40℃~+85℃
Humidity: 20~70%
Contact Resistance: ≤30mΩ
Insulation Resistance: ≥500MΩ
Dielectric Strength: 500V AC/(50HZ)/Min
Mating And Unmating Force: 3~20N
Durability: 750 Cycles Min

Material Specification
Housing :Thermo-plastic, UL94V-0.
Contact :Alloy Copper
Shield :Alloy Copper
Please refer to the customer drawing when customer has specified



2	插 针	PHOSPHOR BRONZE	24	FU ^o	
1	塑 座	PA46	1	BLACK	
序号	名 称	材 料	数 量	镀层/颜色	备 注
 温州瑞川电子有限公司 WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.					
一 般 公 差		品 名:	RCH-5366-13 全塑 黑座		
30~	±0.25	料 号:	536613-80000010AB22 (WR44069)		
10~30	±0.20	型 号:	RJ45	图 号:	
~10	±0.15	版 本:	单位:mm	比例: 1:1	纸张: A4
角 度:	±2°	页 面:	1 of 1		

网络插座外形图

绘 图: 吴素飞 日 期: 2022.5.18
审 核: 王清德 日 期: 2022.5.18
核 准: 王 日 期:

改 变 美 观 上 面 图 在 止 兼

A/0 新出版发行

版 次 变 更 履 历

变更单号 绘 制 日 期

该 图 面 供 温 州 瑞 川 电 子 有 限 公 司 内 部 使 用 , 不 得 私 自 复 印