






CIRCUIT DIAGRAM



## The Main Thchnology Performance

|                      |              |
|----------------------|--------------|
| Rate voltage,current | 50mA DC12V   |
| Contact resistance   | ≤100mΩ       |
| Operating force      | ±30gf        |
| Travel               | 0.35±0.10mm  |
| Insulated resistance | ≥100MΩ       |
| Dielectric strength  | ≥250VAC/1min |



PCB.WELDING DRAWING

|      |             |          |     |             |
|------|-------------|----------|-----|-------------|
| E    | 按钮          | PPA      | 1   | 黑色          |
| D    | 盖板          | 铁盖板      | 1   | 镀铜锡         |
| C    | 弹片          | 不锈钢      | 1   | 镀银          |
| B    | 本体          | PPA      | 1   | 黑色          |
| A    | 卡件          | 黄铜       | 1   | 镀银          |
| ITEM | DESCRIPTION | MATERIAL | QTY | FINSH/COLOR |

T S O 1 5 - C B W 1

力度: 高度:  
F: 250G H4.3  
E: 180G H4.5  
.....

| H   | H   | H    | H    | H    |
|-----|-----|------|------|------|
| 4.3 | 6.5 | 9.5  | 12.5 | 15.5 |
| 4.5 | 7.0 | 10.0 | 13.0 | 16.0 |
| 4.8 | 7.5 | 10.5 | 13.5 | 16.5 |
| 5.0 | 8.0 | 11.0 | 14.0 | 17.0 |
| 5.5 | 8.5 | 11.5 | 14.5 | 17.5 |
| 6.0 | 9.0 | 12.0 | 15.0 | 18.0 |

| DIMENSION IN mm                      |          | 厦门市辛译精密电子有限公司<br>Xiamen XinYi Xyeconn Electronics Co.,Ltd |                                                                                             |           |                  |        |
|--------------------------------------|----------|-----------------------------------------------------------|---------------------------------------------------------------------------------------------|-----------|------------------|--------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED |          |                                                           |                                                                                             |           |                  |        |
| .X±0.35                              | .X°± 5°  | APR.<br>Alex                                              | TITLE: 12x12 DIP TACT SWITCH                                                                |           |                  |        |
| .XX±0.25                             | .X°± 3°  | CHK.<br>Jack                                              | DWG NO. TS015-CBW1FHX                                                                       |           |                  |        |
| .XXX±0.15                            | .XX°± 1° | DRA.<br>Can                                               | PROJ.  |           | CUSTOMER DRAWING |        |
|                                      |          |                                                           | SIZE A4                                                                                     | SCALE 1:1 | SHEET 1/1        | REV. A |

厦门市辛译精密电子有限公司  
Xiamen XinYi Xyecom Electronics Co.,Ltd