









contact arrangement



60 press-in contacts

☒ = position with contact

☐ = position without contact



2 hole diameter is to be co-ordinated with the respective contact

1 recommended configuration of plated holes and further information see: DS 09032100001

09 03 260 6840	2
09 03 260 2840	1
part no.	performance level 1

All Dimensions in mm Original Size DIN A3		Scale 1:1	Free size tol. IEC 60603-2		Ref. Sub.	
	All rights reserved	Created by STORCK	Inspected by ZWHR	Standardisation HOFFMANN	Date 2017-05-19	State Final Release
	Department EC PD - DE	Title DIN Signal type M60-flat female press-in 13.0 60-pole				Doc-Key / ECM-Nr. 100072218/UGD/096/D 500000119521
HARTING Electronics GmbH D-32339 Espelkamp		Type TB	Number 0903260X840		Rev. D	Page 1/1