


# Product data sheet

Specifications



## Limit switch lever, 9007, Snap arm c +options

9007AA1

### Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch lever
Device short name	9007C
Associated head	9007T10 9007A 9007C 9007T5 9007N 9007B
Associated complete product	9007C 9007AW
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 22.35 mm - offset: - -
Type of roller	1 steel outside roller diameter: 16.00 mm - width: 6.35 mm
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Switch actuation	By 30° cam
Net weight	0.05 kg

### Environment

Ambient air temperature for operation	-29...85 °C
Ambient air temperature for storage	-29...85 °C
Environmental characteristic	Standard environment

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.462 cm
Package 1 Width	17.78 cm

<b>Package 1 Length</b>	19.304 cm
<b>Package 1 Weight</b>	45.359 g
<b>Unit Type of Package 2</b>	S01
<b>Number of Units in Package 2</b>	100
<b>Package 2 Height</b>	15 cm
<b>Package 2 Width</b>	15 cm
<b>Package 2 Length</b>	40 cm
<b>Package 2 Weight</b>	4.8 kg

## Offer Sustainability

<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Not applicable, out of EU RoHS legal scope
<b>California proposition 65</b>	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Recommended replacement(s)