




| NO. | ECN NO. | DESCRIPTION | DATE |
|-----|---------|-------------|------|
| 1 | | | |




SPECIFICATIONS:
 Current Rating: 3 Amps
 Voltage Rating: 125V AC/DC
 Insulator Resistance: 1000 MΩ Min.
 Contact Resistance: 20mΩ Max.
 Dielectric Withstanding: AC 1000V
 Operating Temp.: -25° C~+125° C
 Contact Material: Brass
 Housing Material: PA9T/PA6T UL94V-0
 Plated: Gold flash all over Nickel
 Packing: PE Bag (Bulk)
未标示公差: 正负0.20mm



Part number information:
 YZT1069-06120-**-025-01

- A、Serial No.
YZT1069: 180° DIP male header
- B、Needle size:
Diameter * total
- C、NO. of positions:
2*01-2*40pins
- D、Spacing:
025: PH2.54mm
- E、Manner of packing
01: loose

| | | | Label | | |
|------|---|---|-------|-------|------|
| | | | C16 | 6.00 | 1.20 |
| | | | C15 | 5.84 | 2.50 |
| | | | C14 | 15.5 | 3.00 |
| | | | C13 | 7.00 | 3.00 |
| | | | C12 | 4.50 | 2.54 |
| | | | C11 | 8.26 | 3.00 |
| | | | C10 | 5.80 | 3.00 |
| | | | C09 | 18.0 | 8.00 |
| | | | C08 | 6.50 | 3.00 |
| | | | C07 | 6.80 | 3.00 |
| | | | C06 | 24.5 | 3.70 |
| | | | C05 | 6.00 | 3.70 |
| | | | C04 | 18.50 | 3.00 |
| | | | C19 | 3.00 | 3.00 |
| | | | C18 | 2.10 | 3.50 |
| | | | C17 | 6.10 | 2.40 |
| Code | A | C | Code | A | C |



深圳市鑫扬泽电子有限公司



| | | | |
|--------|------------|------------|-----|
| SCALE: | N/A | UNIT | mm |
| SHEET: | 1 of 1 | PROJECTION | |
| DATE: | 2018.04.12 | VER. | A.0 |

THE UNMARKED TOLERANCE ARE AS BELOW :

| LENGTH | | ANGLE | |
|--------|---------|-------|--------|
| X.XX | ±0.05mm | X.XX | ±0.50° |
| X.X | ±0.10mm | X.X | ±1.00° |
| X. | ±0.20mm | X. | ±2.00° |

| | | | |
|--------------|--|----------|-----------------|
| DESIGNED BY: | | DWG. NO. | YZT1069-06120系列 |
| CHECKED BY: | | TITLE: | Pogo pin |
| APPROVED BY: | | | |