


SECTION A-A

适用扁平线


适用线路板



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC(等效)。
4. 接触电阻:  $\leq 0.03\Omega$ 。
5. 绝缘电阻:  $\geq 500M\Omega$ 。

技术详询



| 序号 | 品名                 | 材质             |
|----|--------------------|----------------|
| ①  | 0.5拉拔三代胶芯 (H2.0)   | LCP UL94V-0 本色 |
| ②  | 0.5拉拔三代下接端子 (H2.0) | 磷青铜/表面镀锡       |
| ③  | 0.5拉拔三代后盖 (H2.0)   | LCP UL94V-0 黑色 |
| ④  | 0.5拉拔三代焊片 (H2.0)   | 黄铜/表面镀锡        |

| CKT | DIM A | DIM B | DIM C | DIM D | CKT | DIM A | DIM B | DIM C | DIM D |
|-----|-------|-------|-------|-------|-----|-------|-------|-------|-------|
| 4   | 1.50  | 2.56  | 7.60  |       | 33  | 16.00 | 17.06 | 22.10 | 5.20  |
| 5   | 2.00  | 3.06  | 8.10  |       | 34  | 16.50 | 17.56 | 22.60 |       |
| 6   | 2.50  | 3.56  | 8.60  |       | 35  | 17.00 | 18.06 | 23.10 |       |
| 7   | 3.00  | 4.06  | 9.10  |       | 36  | 17.50 | 18.56 | 23.60 |       |
| 8   | 3.50  | 4.56  | 9.60  |       | 37  | 18.00 | 19.06 | 24.10 |       |
| 9   | 4.00  | 5.06  | 10.10 |       | 38  | 18.50 | 19.56 | 24.60 |       |
| 10  | 4.50  | 5.56  | 10.60 |       | 39  | 19.00 | 20.06 | 25.10 |       |
| 11  | 5.00  | 6.06  | 11.10 |       | 40  | 19.50 | 20.56 | 25.60 |       |
| 12  | 5.50  | 6.56  | 11.60 |       | 41  | 20.00 | 21.06 | 26.10 |       |
| 13  | 6.00  | 7.06  | 12.10 |       | 42  | 20.50 | 21.56 | 26.60 |       |
| 14  | 6.50  | 7.56  | 12.60 |       | 43  | 21.00 | 22.06 | 27.10 |       |
| 15  | 7.00  | 8.06  | 13.10 |       | 44  | 21.50 | 22.56 | 27.60 |       |
| 16  | 7.50  | 8.56  | 13.60 |       | 45  | 22.00 | 23.06 | 28.10 |       |
| 17  | 8.00  | 9.06  | 14.10 |       | 46  | 22.50 | 23.56 | 28.60 |       |
| 18  | 8.50  | 9.56  | 14.60 | 5.20  | 47  | 23.00 | 24.06 | 29.10 | 5.75  |
| 19  | 9.00  | 10.06 | 15.10 |       | 48  | 23.50 | 24.56 | 29.60 |       |
| 20  | 9.50  | 10.56 | 15.60 |       | 49  | 24.00 | 25.06 | 30.10 |       |
| 21  | 10.00 | 11.06 | 16.10 |       | 50  | 24.50 | 25.56 | 30.60 |       |
| 22  | 10.50 | 11.56 | 16.60 |       | 51  | 25.00 | 26.06 | 31.10 |       |
| 23  | 11.00 | 12.06 | 17.10 |       | 52  | 25.50 | 26.56 | 31.60 |       |
| 24  | 11.50 | 12.56 | 17.60 |       | 53  | 26.00 | 27.06 | 32.10 |       |
| 25  | 12.00 | 13.06 | 18.10 |       | 54  | 26.50 | 27.56 | 32.60 |       |
| 26  | 12.50 | 13.56 | 18.60 |       | 55  | 27.00 | 28.06 | 33.10 |       |
| 27  | 13.00 | 14.06 | 19.10 |       | 56  | 27.50 | 28.56 | 33.60 |       |
| 28  | 13.50 | 14.56 | 19.60 |       | 57  | 28.00 | 29.06 | 34.10 |       |
| 29  | 14.00 | 15.06 | 20.10 |       | 58  | 28.50 | 29.56 | 34.60 |       |
| 30  | 14.50 | 15.56 | 20.60 |       | 59  | 29.00 | 30.06 | 35.10 |       |
| 31  | 15.00 | 16.06 | 21.10 |       | 60  | 29.50 | 30.56 | 35.60 |       |
| 32  | 15.50 | 16.56 | 21.60 |       |     |       |       |       |       |

深圳市金航标电子有限公司 www.kinghelm.com.cn

KH-CLO.5-H2.0-28PIN-SMT 0755-28190160

|             |                           |            |        |
|-------------|---------------------------|------------|--------|
| 品名 (TITLE)  | 0.5 Pitch拉拔三代卧式下接 (H=2.0) | 制图 (DR)    | 王涛     |
| 校对 (CHKD)   |                           | 审核 (APPR)  | 吴鹏     |
| 科号 (DWG.NO) |                           | 张数 (SHEET) | 1 OF 1 |
| 比例 (SCALE)  | 1:1                       | 单位 (UNITS) | mm     |
| 尺寸 (SIZE)   |                           | 版数 (REV)   | 1      |