

Product data sheet

Specifications



Limit switch head, Limit switches XC Standard, ZCE, M12 metal end plunger

ZCEF0

Main

Range of produc	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	M12 plunger head
Product compatibility	XCKT XCKP XCMD XCKD
Associated body	ZCMD29C12 ZCMD81L5 ZCMD39L5 ZCMD37L2 ZCMD69C12 ZCMD37L5 ZCMD21L08R12 ZCMD39L2 ZCMD39L1 ZCMD25L1 ZCMD41L2 ZCMD61M12 ZCMD29L1 ZCMD21L5 ZCMD41L5 ZCMD25L5 ZCMD21C12 ZCMD61C12 ZCMD81L2 ZCMD21L2 ZCMD29L5 ZCMD37L1 ZCMD21M12 ZCMD81L1 ZCMD25L2 ZCMD29L2 ZCMD21L1 ZCMD41L1 ZCMD21L08U78
Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach, 1 direction
Complementary	
Positive opening	With

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	3.3 cm
Package 1 Length	1.5 cm
Package 1 Weight	31.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)