




SECTION A-A



适用扁平线

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C~85° C.
3. 额定电压: 50V, AC/DC(等效).
4. 接触电阻: ≤0.03Ω.
5. 绝缘电阻: ≥500MΩ

一般公差 (TOLERANCE)
 X ±.60 XX ±1.0
 Y ±.20 XXX ±.05
 ANGLES ±1°

| 序号 | 品名 | 材质 |
|----|--------------------|----------------|
| ① | 0.5拉拔三代胶芯 (H2.0) | LCP UL94V-0 本色 |
| ② | 0.5拉拔三代上接端子 (H2.0) | 磷青铜/表面镀锡 |
| ③ | 0.5拉拔三代后盖 (H2.0) | LCP UL94V-0 黑色 |
| ④ | 0.5拉拔三代焊片 (H2.0) | 黄铜/表面镀锡 |

| CKT | DIM A | DIM B | DIM C | DIM D | CKT | DIM A | DIM B | DIM C | DIM D |
|-----|-------|-------|-------|-------|-----|-------|-------|-------|-------|
| 1 | 1.50 | 2.56 | 7.60 | | 33 | 16.00 | 17.06 | 22.10 | |
| 5 | 2.00 | 3.06 | 8.10 | | 34 | 16.50 | 17.56 | 22.60 | 5.20 |
| 6 | 2.50 | 3.56 | 8.60 | | 35 | 17.00 | 18.06 | 23.10 | |
| 7 | 3.00 | 4.06 | 9.10 | | 36 | 17.50 | 18.56 | 23.60 | |
| 8 | 3.50 | 4.56 | 9.60 | | 37 | 18.00 | 19.06 | 24.10 | |
| 9 | 4.00 | 5.06 | 10.10 | | 38 | 18.50 | 19.56 | 24.60 | |
| 10 | 4.50 | 5.56 | 10.60 | | 39 | 19.00 | 20.06 | 25.10 | |
| 11 | 5.00 | 6.06 | 11.10 | | 40 | 19.50 | 20.56 | 25.60 | |
| 12 | 5.50 | 6.56 | 11.60 | | 41 | 20.00 | 21.06 | 26.10 | |
| 13 | 6.00 | 7.06 | 12.10 | | 42 | 20.50 | 21.56 | 26.60 | |
| 14 | 6.50 | 7.56 | 12.60 | | 43 | 21.00 | 22.06 | 27.10 | |
| 15 | 7.00 | 8.06 | 13.10 | | 44 | 21.50 | 22.56 | 27.60 | |
| 16 | 7.50 | 8.56 | 13.60 | | 45 | 22.00 | 23.06 | 28.10 | |
| 17 | 8.00 | 9.06 | 14.10 | | 46 | 22.50 | 23.56 | 28.60 | |
| 18 | 8.50 | 9.56 | 14.60 | 5.20 | 47 | 23.00 | 24.06 | 29.10 | 5.75 |
| 19 | 9.00 | 10.06 | 15.10 | | 48 | 23.50 | 24.56 | 29.60 | |
| 20 | 9.50 | 10.56 | 15.60 | | 49 | 24.00 | 25.06 | 30.10 | |
| 21 | 10.00 | 11.06 | 16.10 | | 50 | 24.50 | 25.56 | 30.60 | |
| 22 | 10.50 | 11.56 | 16.60 | | 51 | 25.00 | 26.06 | 31.10 | |
| 23 | 11.00 | 12.06 | 17.10 | | 52 | 25.50 | 26.56 | 31.60 | |
| 24 | 11.50 | 12.56 | 17.60 | | 53 | 26.00 | 27.06 | 32.10 | |
| 25 | 12.00 | 13.06 | 18.10 | | 54 | 26.50 | 27.56 | 32.60 | |
| 26 | 12.50 | 13.56 | 18.60 | | 55 | 27.00 | 28.06 | 33.10 | |
| 27 | 13.00 | 14.06 | 19.10 | | 56 | 27.50 | 28.56 | 33.60 | |
| 28 | 13.50 | 14.56 | 19.60 | | 57 | 28.00 | 29.06 | 34.10 | |
| 29 | 14.00 | 15.06 | 20.10 | | 58 | 28.50 | 29.56 | 34.60 | |
| 30 | 14.50 | 15.56 | 20.60 | | 59 | 29.00 | 30.06 | 35.10 | |
| 31 | 15.00 | 16.06 | 21.10 | | 60 | 29.50 | 30.56 | 35.60 | |
| 32 | 15.50 | 16.56 | 21.60 | | | | | | |

深圳市金航标电子有限公司 www.kinghelm.com.cn

KH-CL0.5-H2.0-14PS-SMT 0755-28190160

| | | | |
|-------------|---------------------------|-----------|-----|
| 品名 (TITLE) | 0.5 Pitch拉拔三代卧式上接 (H=2.0) | 制图 (DR) | 王涛 |
| 校对 (CHKD) | | 审核 (APPD) | 吴鹏 |
| 科号 (DWG.NO) | | 审核 (APPD) | 黄志明 |

| | | | | | | | | | |
|------------|-----|------------|----|------------|--------|-----------|----|-----|---|
| 比例 (SCALE) | 1:1 | 单位 (UNITS) | mm | 张数 (SHEET) | 1 OF 1 | 尺寸 (SIZE) | A4 | REV | 1 |
|------------|-----|------------|----|------------|--------|-----------|----|-----|---|