



| Part No | Pin | A | B |
|-------------------|-----|-------|-------|
| WAFER-ZH1.5-2PJK | 2 | 1.50 | 3.30 |
| WAFER-ZH1.5-3PJK | 3 | 3.00 | 4.80 |
| WAFER-ZH1.5-4PJK | 4 | 4.50 | 6.30 |
| WAFER-ZH1.5-5PJK | 5 | 6.00 | 7.80 |
| WAFER-ZH1.5-6PJK | 6 | 7.50 | 9.30 |
| WAFER-ZH1.5-7PJK | 7 | 9.00 | 10.80 |
| WAFER-ZH1.5-8PJK | 8 | 10.50 | 12.30 |
| WAFER-ZH1.5-9PJK | 9 | 12.00 | 13.80 |
| WAFER-ZH1.5-10PJK | 10 | 13.50 | 15.30 |
| WAFER-ZH1.5-11PJK | 11 | 15.00 | 16.80 |
| WAFER-ZH1.5-12PJK | 12 | 16.50 | 18.30 |
| WAFER-ZH1.5-13PJK | 13 | 18.00 | 19.80 |
| WAFER-ZH1.5-14PJK | 14 | 19.50 | 21.30 |
| WAFER-ZH1.5-15PJK | 15 | 21.00 | 22.80 |
| WAFER-ZH1.5-16PJK | 16 | 22.50 | 24.30 |
| WAFER-ZH1.5-17PJK | 17 | 24.00 | 25.80 |
| WAFER-ZH1.5-18PJK | 18 | 25.50 | 27.30 |
| WAFER-ZH1.5-19PJK | 19 | 27.00 | 28.80 |
| WAFER-ZH1.5-20PJK | 20 | 28.50 | 30.30 |

技术要求Specification:

- 1、材质Material: PA66 UL94V-2;
- 2、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

| | | | |
|---------------------------------------|---------|---|---------------------------|
| MANUFACTURE DWG | |  东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd | |
| UNLESS OTHERWISE SPECIFIED TOLERANCES | |  | TITLE: ZH1.5MM HOUSING |
| | | | PAR WAFER-ZH1.5-NPJK |
| DECIMALS: | ANGLES: | | DWN |
| .X±0.30 | X.*±1° | | CHKD |
| .XX±0.20 | | APVD | SCALE 1:1 UNIT:MM |
| .XXX±0.10 | | CUSTOMER COPY | SIZE:A4 SHEET:1F1 |
| | | | REV:A |