



		1	
Part Number:		DRAWN	2/10/2017
CM10	1004 1	CJ	3/10/2017
2MTQ	1004-1	CHECKED	10/6/2017
		P.D.	10/0/2017
Description:	namic Speaker	APPROVED	10/6/2017
Waterproof Dy		C.E.	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


## Top View



## Side View



## **Bottom View**



		REVISION HISTORY						
Items	Specifications	Conditions	REV	DESCRIPTION	DATE	APPROVED		
Sound Pressure Level	92	dB (@ 10cm), Avg.		Released from Engineering	10/6/2017	C.E.		
Resonant Frequency	900	Hz	1	Added polarity marking	10/25/2017	C.E.		
Frequency Range	900 ~ 10,000	Hz	2	Update height, add detail to bottom view	3/21/2018	C.E.		
Nominal Power	1	W	3	Update frequency range, resonant frequency	4/10/2018	C.E.		
Max. Power	1.2	W	4	Updated height tolerance	4/20/2018	C.E.		
Impedance	4	Ω	5	Updated height, general tolerance	4/26/2018	C.E.		
Cone Material	Mylar			NOTES /				
Mount Type	Flush Mount			All dimensions are in mm unless otherwise noted				
IP Rating	IP67			2) All tolerances are ± 0.5 mm unless otherwise noted				
Storage Temperature	-20 ~ +55	°C		3) All parts meet RoHS				
Operating Temperature	-20 ~ +55	°C		4) Subject to change or redrawn without notice				