

Tel: 1-800-722-8197 1-631-595-2217 Fax: 1-631-667-5484 EMAIL: sales@challelec.com WEB: www.challengeelectronics.com ISO 9001/14001:2015 Certified

INDICATORS • SPEAKERS • SOUND TRANSDUCERS • ENCLOSURES • MICROPHONES • BATTERY ACCESSORIES

CS17-01P100-03-1X

Rev. 2-2022 RoHS3 & REACH IP67 Front Face Mobile Speakers




Operating Characteristics ELECTRICAL 110 Rated Power 1 W **Short Term** 100 1.2 W Max Power 8 Ω ± 15 % Impedance 90 2000 Hz; 1 W ACOUSTIC: 1CC Sealed Enclosure 80 (GB) 1000 Hz ± 20 % fo 70 1000 to 10000 Hz Freq. Range 99 ± 3 dB Rated SPL 2000 Hz; 60 1 W; 10 cm; <10 % Distortion 50 1000 Hz; 1 W 40 100 10000

Physical Characteristics

TEMPERATURE RANGES

Operating	-20 to +70 °C
Storage	-40 to +85 °C

Weight 2.1 g



Frequency (Hz)

General tolerance = ± 0.2 mm and all measurements in mm unless otherwise noted.

Revision	Description	Ву	Date
1-2020	Added default unit of measurement (mm)	WS	2020-09-10
2-2022	Added minimum diaphragm clearance requirement callout to the mechanical drawing. Added product photo.	CT	2022-05-06

Warranty: For a period of one (1) year from date of shipping under normal operations conditions. This warranty does not apply to products damaged through misuse, abuse, improper installation, alteration, rework, or attempt to repair.

The information contained herein is believed to be correct, but no guarantee or warranty, express or implied, with respect to accuracy, completeness or results is extended and no liability is assumed. Challenge Electronics reserves the right to make changes in any specification, data or material contained herein.