






- ① HOUSING MATERIAL: GLASS-FILLED POLYMER.
- ② POST MATERIAL: COPPER ALLOY.
- ③ POST FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- ④ MARKING ON THIS SIDE.
- ⑤ RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
- ⑥ PART NUMBER, DATE CODE MARKED THIS APPROXIMATE AREA.



SECTION Z-Z

REFERENCE FAMILY DRAWING 650473 FOR ALL TYPE C HEADER OFFERINGS



PC BOARD LAYOUT

1-50	X	X	X	150	5650907-5
POSITIONS LOADED	C	B	A	NO. OF LOADED POSITION	ASSY PART NUMBER
	ROWS LOADED				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN J. POLIGNONE	OSMAYOS	 TE Connectivity		
0 PLC ± -	1 PLC ± -	APVD A. SHARPE	OSMAYOS			
2 PLC ± 0.13[.005]	3 PLC ± -	NAME	OSMAYOS			
4 PLC ± -	ANGLES ± -	PRODUCT SPEC	OSMAYOS			
MATERIAL	FINISH	APPLICATION SPEC		ASSEMBLY, PIN, EUROCARD, TYPE C, 150 POSITION, 2.64[.104] SOLDER POST		
		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			A1	00779	5650907	
		CUSTOMER DRAWING	SCALE	5:1	SHEET	1 OF 1
						REV A