

(1,00 mm) .0394"

# W PROFILE & ELEVATED ONE PIECE

#### **SPECIFICATIONS**

For complete specifications and recommended PCB layouts see www.samtec.com?FSI

Insulator Material: Liquid Crystal

Polymer Contact Material:

BeCu Current Rating:

2.8 A per pin

(1 pin powered per row)

Operating Temp Range:
-55°C to +125°C

Plating: Au over 50μ" (1,27 μm) Ni RoHS Compliant:

## Processing: Lead-Free Solderable:

SMT Lead Coplanarity: (0,10 mm) .004" max (05-30) (0,15 mm) .006" max (50) Compression Board: Gold Pads required

#### RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note: Applications requiring 40-50 positions without threaded inserts, please contact Samtec Interconnect Processing Group.

Note: Some lengths, styles and options are non-standard, non-returnable.

#### **Other Solutions**








### **ALSO AVAILABLE** (MOQ Required)


- No alignment pin
- Top side alignment pin
- Bottom side alignment pin
- Other platings

Contact Samtec.










Double Row Version -03, -06, -10

Insert Option (50 pins/row)

BODY HEIGHT	Α	В
-03	(3,00) .118	(8,76) .345
-06	(6,00) .236	(9,02) .355
-10	(10,00) .394	(9,02) .355




(1,60)

Single Row Version -03, -06, -10

Short Version





#### **ALIGNMENT ROW OPTION** OTHER OPTION **INSERT OPTION OPTION** Leave blank for no Alignment Pin Leave blank for Short Version -WT (No screw down inserts or holes) = Single Row (Available with 5, 10 & 20 = Weld Tab (Available with -S row option & –E -AD pins with -AD alignment pin) -06 & -10 body height only) = Alignment Pin Top & Bottom = #2-56 x 1/16" screw thread -D -M= Double Row = Polyimide Film Pick & Place Pad = 2,00 mm x 0,40 mm screw thread (50 position with threaded insert option only) (71,20) 2.803= Plastic Pick & Place Pad (5,08 mm) .200" x (12,45 mm) .490" (50 not available with –E) (Not available with –S row option or –03 body height) Insert Option (50 pins/row) (No. of positions x (1,00) .03937) + (5,00).197 -TR = Tape & Reel Packaging (4,60) .181 (5.30).209 \_(No. of positions x (1,00) .03937) \_\_\_\_\_ -03, -06 & -10 - (0,36) .014 **Contact Detail**

(1,40) .055

(2,25) .089

-WT Option (-06 & -10 Body only)

-03-AD Shown

(No. of positions x (1,00) .03937) + (14,70) .579

Insert Option (10, 20 & 30 pins/row)