


# Kinghelm®

REV		REVISIONS		
NUMBER	DESCRIPTION	DWN	CHK	DATE
A	DESIGN			



**NOTES:**

1. ELECTRICAL:
  - 1.1. VOLTAGE RATING:DCV 300V 10MS
  - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
  - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES
2. MATERIAL:
  - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
			AS
②	接头	1代 IPEX端子	1
①	同轴线	RF0.81黑色同轴线, OD:0.81mm	AS

深圳市金航标电子有限公司

www.kinghelm.com.cn

KHA-(RG0.81)-TX180-IPEX-221

0755-28190160

ALL DIMENSION ARE IN MM	DRAWN	Jamy	DATE	2020-06-15
	ENG.			
COMPUTER GENERATED IN SOLIDWORKS	MFG.			
	Q.A.			

PROJECTION	GENERAL TOLERANCE FOR ANGLES	X.X	X.XX	X.XXX
		± 1°	± 0.3	± 0.25 ± 0.150

SIZE	Number	REV	A
SCALE:	Free	TYPE	SHEET 1 OF 1

CUSTOMER PIN:

