


# Kinghelm®

REV		REVISIONS		
NUMBER	DESCRIPTION	DWN	CHK	DATE
A	DESIGN			



**NOTES:**

1. ELECTRICAL:
  - 1.1. VOLTAGE RATING:DCV 300V 10MS
  - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
  - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES
2. MATERIAL:
  - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
			AS
②	接头	1代 IPEX端子	1
①	同轴线	RF1.37黑线,OD:1.37mm	AS

深圳市金航标电子有限公司

www.kinghelm.com.cn

KHA-(RG1.37)-TX60-IPEX-221

0755-28190160

ALL DIMENSION  
ARE IN MM

DRAWN  
Jamy

DATE  
2020-06-15

ENG.

COMPUTER GENERATED  
IN SOLIDWORKS

MFG.

DO NOT SCALE  
THIS DRAWING

Q.A.



GENERAL TOLERANCE FOR  
ANGLES X.X X.XX X.XXX  
± 1° ± 0.3 ± 0.25 ± 0.150

SIZE Number

B

REV

A

CUSTOMER PIN:

SCALE: Free

TYPE

SHEET 1 OF 1