




技术特性/Specifications:

额定电压 Rated voltage: 100V AC, DC
额定电流 Rated current: 3A AC, DC
接触电阻 Contact resistance: 20m Ω max
绝缘电阻 Insulation resistance: 1000M Ω min
耐压 Withstand voltage: 1000V AC/minute
环境温度 Ambient temperature: -40 $^{\circ}$ C $\sim$ +105 $^{\circ}$ C
适用线规 Wire range: AWG#26 $\sim$ #22

A

B

C






D

E

F

12345678

REV.	REVISION DESCRIPTION	DATE	APPD
B	外形尺寸作调整	22. 7. 4	Wuhui



A

B

C

D

E

F


NOTES

Available in 10 Circuits.
Mates with DL20023-Y Series Housing.
Material : LCP UL94V-0.
Pin Material : Brass.Tin-plated .
Green Material RoHS Compliant.


3	③	基座	LCP	1	UL94V-0
2	②	焊片	黄铜	2	镀锡
1	①	接触件	黄铜	N*	镀锡
序号	图号	名称	材料	数量	附件

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
. X: ± 0.30	X° : $\pm 3.0^\circ$	PRODUCT NAME: DL20023-10AWB	
. XX: ± 0.15	. X° : $\pm 2.0^\circ$	TITLE: 2.00 mm Pitch Wire To Board SMT Wafer	
. XXX: ± 0.01	. XX° : $\pm 1.0^\circ$	DR:Chen Quan Long	DATE:22. 05. 19
FINISH: _____		CHKD: Wu Hui	DATE:22. 05. 19
DRAWING NO: GC-DL20023-XXWB-XXX-XX-X-XX		APPD: Ren An De	DATE:22. 05. 19
		PART NO: DL20023-XXWB-XXX-XX-X-XX	
		SCALE: N/A	PAGE:1/1
		UNITS: mm	REV. : B


12345678




DL20023-2AS




DL20023-6AS





DL20023-3AS



DL20023-8AS



DL20023-4AS



P.C.B LATOUT

- NORES:
1. Rated voltage: 100V AC.DC
 2. Rated current: 3A AC DC
 3. Contact resistance: $\leq 15 \text{ m}\Omega$
 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 5. Withstand voltage: 1000V AC/minute
 6. Ambient temprature: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$
 7. Materials: PBT UL94V-0(2).
 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.30	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL20023-AS		TITLE: 2.0 mm Pitch Wire To Board Wafer	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR:Yuan Jun Rong DATE:20.10.12		PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui DATE:20.10.12		SCALE: N/A	PAGE:1/2
DRAWING NO:		APPD:Ren An De DATE:20.10.12		UNITS: mm	REV.: A

A

B

C

D

E

F

A

B


C

D


E

F

DL20023-2AWS





DL20023-3AWS




- NORES:
- 1. Rated voltage: 100V AC.DC
 - 2. Rated current: 3A AC DC
 - 3. Contact resistance: $\leq 15 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$
 - 7. Materials: PBT UL94V-0(2).
 - 8. Matched RoHS criteria

DL20023-4AWS



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.30	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL20023-AWS		TITLE: 2.0 mm Pitch Wire To Board Wafer	
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DR:Yuan Jun Rong	DATE:20.10.12	PART NO:	
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:20.10.12	SCALE: N/A	PAGE:1/3
DRAWING NO:		APPD:Ren An De	DATE:20.10.12	UNITS: mm	REV. : A



REV.	REVISION DESCRIPTION	DATE	APPD
------	----------------------	------	------

- NORES:
1. Rated voltage: 100V AC.DC
 2. Rated current: 3A AC DC
 3. Contact resistance: $\leq 15\text{ m}\Omega$
 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 5. Withstand voltage: 1000V AC/minute
 6. Ambient temperature: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$
 7. Materials: PBT UL94V-0(2).
 8. Matched RoHS criteria

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.30	X° : ± 3.0°	PRODUCT NAME:		TITLE: 2.0 mm Pitch	
.XX: ± 0.15	.X° : ± 2.0°	DL20023-AWS		Wire To Board Wafer	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Yuan Jun Rong	DATE:20.10.12	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE:20.10.12	SCALE: N/A	PAGE:2/3
DRAWING NO:		APPD:Ren An De	DATE:20.10.12	UNITS: mm	REV. : A

A

B

C

D

E

F

A

B


C

D


E

F


DL20023-12AWS



DL20023-14AWS




- NORES:
- 1. Rated voltage: 100V AC.DC
 - 2. Rated current: 3A AC DC
 - 3. Contact resistance: $\leq 15 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temprature: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$
 - 7. Materials: PBT UL94V-0(2).
 - 8. Matched RoHS criteria




GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.30	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL20023-AWS		TITLE: 2.0 mm Pitch Wire To Board Wafer	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR:Yuan Jun Rong		DATE:20.10.12	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui		DATE:20.10.12	
FINISH:		APPD:Ren An De		DATE:20.10.12	
DRAWING NO:		PART NO:		SCALE: N/A	
		UNITS: mm		PAGE:3/3	
		REV. : A			


DL20023-2Y




DL20023-3Y




DL20023-8Y



DL20023-4Y



DL20023-6Y



NOTES

Available in 02.03.04.06.08 Circuits.
Mates with DL20023 Series Housing.
Material : PBT UL94V-0(2).
Accepts DL20023-T Crimp Terminal.
Green Material RoHS Compliant.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
. X: ± 0.30	X° $\pm 3.0^\circ$	PRODUCT NAME: DL20023-Y		TITLE: 2.0 mm Pitch Housing	
. XX: ± 0.15	. X° $\pm 2.0^\circ$	DR:Chen Quan Long	DATE:21/08/01	PART NO:	
. XXX: ± 0.01	. X° $\pm 1.0^\circ$			SCALE: N/A	
FINISH: _____		CHKD:Wu Hui	DATE:21/08/01	PAGE:1/2	
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	UNITS: mm	REV. : A

A

B


C

D


E

F


DL20023-10Y



DL20023-12Y



DL20023-14Y



NOTES

Available in 10.12.14 Circuits.
Mates with DL20023 Series Housing.
Material : PBT UL94V-0(2).
Accepts DL20023-T Crimp Terminal.
Green Material RoHS Compliant.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
. X: ± 0.30	X° $\pm 3.0^\circ$	PRODUCT NAME: DL20023-Y		TITLE: 2.0 mm Pitch Housing	
. XX: ± 0.15	. X° $\pm 2.0^\circ$	DR:Chen Quan Long	DATE:21/08/01	PART NO:	
. XXX: ± 0.01	. X° $\pm 1.0^\circ$		DATE:21/08/01	SCALE: N/A	PAGE:2/2
FINISH: _____		CHKD:Wu Hui	DATE:21/08/01	UNITS: mm	REV. : A
DRAWING NO:		APPD:Ren An De	DATE:21/08/01		

REV.	REVISION DESCRIPTION	DATE	APPD

A

B




C

D


E

F


1	2	3	4	5	6	7	8		
DL20023-2Y-0.75		DL20023-3Y-0.75		DL20023-8Y-0.75		REV.	REVISION DESCRIPTION	DATE	APPD



DL20023-4Y-0.75



DL20023-6Y-0.75



NOTES

Available in 02.03.04.06.08 Circuits.
Mates with DL20023 Series Housing.
Material : PBT UL94V-0(2).
Accepts DL20023-T Crimp Terminal.
Green Material RoHS Compliant.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.30	X° ± 3.0°	PRODUCT NAME: DL20023-Y-0.75		TITLE: 2.0 mm Pitch Housing	
.XX: ± 0.15	.X° ± 2.0°	DR:Chen Quan Long		DATE:21/08/01	
.XXX: ± 0.01	.X° ± 1.0°	CHKD:Wu Hui		DATE:21/08/01	
DRAWING NO:		APPD:Ren An De		SCALE: N/A	PAGE:1/2
				UNITS: mm	REV.: A

A

B

C

D

E

F

A

B



C

D



E

F



DL20023-10R-0.75



DL20023-12R-0.75




DL20023-14R-0.75



NOTES

- Available in 10.12.14 Circuits.
- Mates with DL20023-Y Series Housing.
- Material : PBT UL94V-0(2).
- Accepts DL20023-RT Crimp Terminal.
- Green Material RoHS Compliant.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.30	X° : $\pm 3.0^\circ$	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X° : $\pm 2.0^\circ$	DL20023-R-0.75		2.0 mm Pitch Wire To Wire Receptacle Housing	
.XXX: ± 0.01	.XX° : $\pm 1.0^\circ$	DR:Chen Quan Long	DATE:21/08/01	PART NO:	
FINISH:		CHKD:Wu Hui	DATE:21/08/01	SCALE: N/A	PAGE:2/2
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	UNITS: mm	REV. : A




DL20023-2R

DL20023-3R

DL20023-8R

REV.	REVISION DESCRIPTION	DATE	APPD




DL20023-4R

DL20023-6R

NOTES

Available in 02.03.04.06.08 Circuits.
Mates with DL20023-Y Series Housing.
Material : PBT UL94V-0(2).
Accepts DL20023-RT Crimp Terminal.
Green Material RoHS Compliant.


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.30	X° : ± 3.0°	PRODUCT NAME: DL20023-R		TITLE: 2.0 mm Pitch Wire To Wire Receptacle Housing	
.XX: ± 0.15	.X° : ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/08/01	SCALE: N/A	
FINISH: _____		CHKD:Wu Hui	DATE:21/08/01	PAGE:1/2	
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	UNITS: mm	REV.: A



NOTES

Available in 10.12.14 Circuits.
Mates with DL20023-Y Series Housing.
Material : PBT UL94V-0(2).
Accepts DL20023-RT Crimp Terminal.
Green Material RoHS Compliant.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.30	X° : ± 3.0°	PRODUCT NAME: DL20023-R		TITLE: 2.0 mm Pitch Wire To Wire Receptacle Housing	
.XX: ± 0.15	.X° : ± 2.0°			PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/08/01	SCALE: N/A PAGE:2/2	
FINISH: _____		CHKD:Wu Hui	DATE:21/08/01		
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	UNITS: mm	REV. : A






REV.	REVISION DESCRIPTION	DATE	APPD

DL20023-2R-0.75

DL20023-3R-0.75

DL20023-8R-0.75



DL20023-4R-0.75

DL20023-6R-0.75



NOTES

Available in 02.03.04.06.08 Circuits.
Mates with DL20023-Y Series Housing.
Material : PBT UL94V-0(2).
Accepts DL20023-RT Crimp Terminal.
Green Material RoHS Compliant.


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.30	X° : ± 3.0°	PRODUCT NAME: DL20023-R-0.75		TITLE: 2.0 mm Pitch Wire To Wire Receptacle Housing	
.XX: ± 0.15	.X° : ± 2.0°				
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/08/01	PART NO:	
FINISH: _____		CHKD:Wu Hui	DATE:21/08/01		
DRAWING NO:		APPD:Ren An De	DATE:21/08/01	SCALE: N/A	PAGE:1/2
				UNITS: mm	REV.: A

DL20023-10Y-0.75

DL20023-12Y-0.75




DL20023-14Y-0.75



NOTES

Available in 10.12.14 Circuits.
Mates with DL20023 Series Housing.
Material : PBT UL94V-0(2).
Accepts DL20023-T Crimp Terminal.
Green Material RoHS Compliant.

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.30	X° $\pm 3.0^\circ$	PRODUCT NAME: DL20023-Y-0.75		TITLE: 2.0 mm Pitch Housing			
.XX: ± 0.15	.X° $\pm 2.0^\circ$	DR:Chen Quan Long		PART NO:			
.XXX: ± 0.01	.X° $\pm 1.0^\circ$	CHKD:Wu Hui		DATE:21/08/01			
FINISH:		APPD:Ren An De		DATE:21/08/01		SCALE: N/A	PAGE:2/2
DRAWING NO:				UNITS: mm		REV.: A	



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Mates with DL20023-Y or DL20023-R Series Housing.

Material : PBT UL94V-0(2).
Green Material RoHS Compliant.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
.X: ± 0.30	X° : ± 3.0°	PRODUCT NAME: DL20023-1E		TITLE: 2.0 mm Pitch Wire To Wire Receptacle Stopper	
.XX: ± 0.15	.X° : ± 2.0°	DR:KeXianQiang	DATE:17.10.12	PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Liu Bing	DATE:17.10.12	SCALE: N/A	PAGE:1/1
FINISH: _____		APPD:Ren An De	DATE:17.10.12	UNITS: mm	REV. : A
DRAWING NO:					

REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL20023-Y Series Housing.

Accepts AWG #26~22 Wire Range.

0.13~ 0.33 mm² .



Insulation O.D.=1.4~1.7mm.

Material : Phosphor Bronze .


Finish: Tin plated.

Qty/Reel: 10,000 PCS.


Thickness: 0.25 mm.



SECTION A-A




SECTION B-B



SECTION C-C

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DL20023-T		TITLE: 2.00 mm Pitch Crimp Terminal			
.XX: ± 0.15	.X°: ± 2.0°	DR:Chen Quan Long		DATE:20/12/23	PART NO:		
.XXX: ± 0.01	.XX°: ± 1.0°	CHKD:Wu Hui		DATE:20/12/23	SCALE: N/A		
FINISH:		APPD:Ren An De		DATE:20/12/23	UNITS: mm		
DRAWING NO:					PAGE: 1/1		
					REV.: A		



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL20023-R Series Housing.

Accepts AWG #26~22 Wire Range.

0.13~ 0.33 mm² .

Insulation O.D.=1.4~1.7mm.

Material : Phosphor Bronze .

Finish: Tin plated.

Qty/Reel: 10,000 PCS.

Thickness: 0.25 mm.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:	TITLE: 2.00 mm Pitch Wire To Wire Crimp Terminal
.XX: ± 0.15	.X° : ± 2.0°	DL20023-RT	PART NO:
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:20/12/23
FINISH:		CHKD:Wu Hui	DATE:20/12/23
DRAWING NO:		APPD:Ren An De	DATE:20/12/23
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A