


PANEL CUT-OUT

TEL: 0769-82310511-867

- Socket : RT-C14B-H00-13-R
 1.Rating : 10A 250VAC (CCC ; UL ; CUL)
 2.Insulation resistance : >100MΩ Min 500VDC
 3.Withstand voltage : >2000VAC 0.5mA 1 minute
 Switch : SS11-BBIWQ-R20-R
 1.Rating : 16A 125/250VAC 12A 125/250VAC (UL ; CUL)
 16(4)A 250V~T125/55 (ENEC17 ; M ; CQC)
 2.Contact resistance : <50mΩ
 3.Insulation resistance : >100MΩ Min 500VDC
 4.Dielectric strength : >1500VAC 0.5mA 1 minute



| | | | | | | | | | | | | | | |
|----|-------------|----|-------------|------------------------|-----------|--|---------|--------|------------|-----------------|-----|---------------------|-------|----|
| 5 | → | 10 | → | DIMENSIONAL TOLERANCES | | APPROVED | CHECKED | DESIGN | DRAWN | ALL SIZE ARE IN | MM | | | |
| 4 | → | 9 | → | RANGE | TOLERANCE | | | | LMC | SCALE | NO | | | |
| 3 | → | 8 | → | X | ±0.15 | | | | 2019.09.12 | MAT'L | *** | DRAWING NO. | REV. | |
| 2 | → | 7 | → | X.X | ±0.10 | | | | | MATERIAL NO. | | | | |
| 1 | → | 6 | → | X.XX | ±0.05 | | | | | | | RT-C14B-H1+SS11-1BB | ***** | A0 |
| NO | DESCRIPTION | NO | DESCRIPTION | ANGLES | ±1' | LECION ELECTRONIC & HARDWARE CO., LTD. | | | | | | | | |