






品名	颜色		印字类型	备注
	上盖	基座		
SS11-EEIWG-R20-R	灰色	灰色	○ -	常规
SS11-BBAWG-R20-R	黑色	黑色	-	常规
SS11-BBDWG-R20-R	黑色	黑色	●	常规
SS11-BBIWG-R20-R	黑色	黑色	○ -	常规
SS11-BBIWG-R20-H	黑色	黑色	○ -	客户特殊要求
SS11-BBIWG-R20-Z	黑色	黑色	○ -	客户特殊要求
SS11-BBKWG-R20-R	黑色	黑色	● -	
SS11-BBTWG-R20-R	黑色	黑色	○ I	常规
SS11-RBDWG-R20-R	红色	黑色	●	常规
SS11-RBIWG-R20-R	红色	黑色	○ -	常规
SS11-GBIWG-R20-R	绿色	黑色	○ -	常规
SS11-RBIWG-R20-B	红色	黑色	○ -	客户特殊要求
SS11-WWIBG-R20-R	白色	白色	○ -	常规
SS11-BBOWG-R20-R	黑色	黑色	Ω Ω	常规
SS11-BBNNG-R20-R	黑色	黑色	□ □	常规
SS11-WWIBG-R20-R(W2)	纯白色	纯白色	○ -	纯白色开关
SS11-EETWG-R20-R	灰色	灰色	○ I	常规
SS11-GBIWG-R20-H	绿色	黑色	○ -	客户特殊要求
SS11-NBOWG-R20-R	棕色	黑色	Ω Ω	常规

PANEL CUTOUT DIMENSION



PANEL THICKNESS	X	Y
0.8~1.2mm	19.2 ^{+0.1} mm	12.9 ^{+0.1} mm
1.3~2.0mm	19.4 ^{+0.1} mm	12.9 ^{+0.1} mm
2.1~2.5mm	19.8 ^{+0.1} mm	12.9 ^{+0.1} mm



1. 电路CIRCUIT: ON/OFF;
2. 快插端子QUICK CONNECTOR TYPE;
3. 额定值RATING: 16A 125/250VAC (UL;C-UL);
12A 125/250VAC (UL;C-UL);
16(4)A 250V~T125/55(ENEC17;NEMKO;CQC;CB)
4. 所有部件均使用环保材料

ALL MATERIALS USE IN CONFORMITY WITH THE RoHS DIRECTIVE

△5	→	△10	→	DIMENSIONAL TOLERANCES	APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN MM	SCALE	NO	LMC 2019.05.20
△4	增加灰色品名 2022.09.14	△9	→	RANGE	TOLERANCE				MAT'L	***		
△3	增加纯白色上盖 2022.06.30	△8	→	X	±0.30				MATERIAL NO.			
△2	增加绿色上盖 2021.06.02	△7	→	X.X	±0.20				DRAWING NO.	REV.		
△1	整理汇编	△6	→	X.XX	±0.10				WIF120070	A4		
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.		SS11-GBIWG-R20-H				