





1. 电路 CIRCUIT: ON/OFF
2. 额定值 RATING: 21A GP 125/250VAC T125/55 (C-UL)
16(6)A 250V~T125/55 (ENEC17)
12(4)A 250V~T85/55 (NEMKO; CQC; KC)
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘阻抗 INSULATION RESISTANCE: >100MΩ
(500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE
6. 所有部件均使用环保材料
ALL MATERIALS USING MEET THE RoHS DIRECTIVE



PANEL THICKNESS	X	Y
0.75~1.25mm	19.2 ⁺⁰ _{-0.1} mm	12.9 ^{+0.1} ₋₀ mm
1.25~2.0mm	19.4 ⁺⁰ _{-0.1} mm	12.9 ^{+0.1} ₋₀ mm



注：与样品的上、下色差不能大于0.5Dk1ta E

品 名	颜 色	
	上 盖	基 座
SS21-G1BIWG8-B	绿色GREEN (色卡3272C)	黑 色
SS21-G1WIWG8-B(W3)	绿色GREEN (色卡3272C)	米白色CREAMY-WHITE

5		10		DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		MM		
4		9		RANGE	TOLERANCE					SCALE	NO			
3		8		X	±0.30					MAT'L	***			
2		7		X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.	
1	更正品名 2023.05.24	6		X.XX	±0.10					SS21-G1WIWG8-B(W3)		WIF123041	A1	
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.								