



P.C.B. LAYOUT

SPECIFICATION

1. Rating: DC 12V 0.3A
  2. Function: 2P2T
  3. Contact Resistance: ≤70m MAX
  4. Operating Force: 180±80gf
  5. Life test: 10,000 cycles
  6. 功能: 自锁
- TEL:0769-82320511-867

				TOLERANCE UNLESS SPECIFIED									
				UP TO 5mm: ±0.1	ANGULAR	1	2015.9.10	初版		liu			
				ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD		
5	CAMSTICK	SUS	1	NATURAL	TITLE:VERTICAL PUSH SWITCH		UNIT : MM	ROHS	DWN				
4	SPRING	SUS	1	NATURAL	MODEL:PB-22E60B-S-C T2.0		SCALE: 5:1	COMPLIANT	CHK'D				
3	CASE	PA66/0.3mm BRASS	1	GREY/Ag PLATED	东莞市六钧电子五金有限公司 LEGION ELECTRONIC&HARDWARE CO.,LTD						APPD		
2	COVER	PBT/PA66	1	BLACK							PRO.AGL:		REV : A
1	KNOB	POM/PA66/0.045mm PBS	1	WHITE/BLACK/Ag CLAD									
NO.	PART NAME	MATERIAL	QTY	FINISHING									