








P. C. B LAYOUT

SCHEMATIC



SPECIFICATION

- Rating : DC 12 1A.
- Contact resistance: $\leq 50m\Omega$.
- Insulation resistance: $\geq 100M\Omega$ (DC500V).
- Withstanding voltage: 500VAC .
- Insertion and extraction force: 3-30N.
- life test: 5,000 cycles.
- Operation temperature range: $-25^{\circ}C \sim 85^{\circ}C$.
- Sign"* "is importance dimension.

					TOLERANCE UNLESS SPECIFIED									
					UP TO 5mm:±0.1	ANGULAR	1							
					ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD	
5	FLAT PIECE	5	BRASS	1	SN-PLATED	TITLE: PHONE JACK			UNIT : MM	ROHS	DWN			
4	CURVE PIECE	4	MN STEEL	1	SN-PLATED	MODEL: LEC-PJ-202			SCALE: 1:1	COMPLIANT	CHK'D			
3	SPRING	3	BRASS	1	SN-PLATED	东莞市六钧电子五金有限公司					APPD			
2	SLEEVE		BRASS	1	SN-PLATED									
1	HOUSING		PBT	1										
NO.	PART	NAME	MATERIAL	QTY	FINISHING						PRO.AGL:		REV :A0	