



- SPECIFICATIONS**
1. Current Rating: 1A AC, DC
 2. Voltage Rating: 50V AC, DC
 3. Temperature Range: -25°C ~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 100mΩ Min
 6. Withstanding Voltage: 500V AC/minute
 7. Material: Wafer LCP, UL94-V0
PIN Phosphoric bronze Tin-plated
Solder pad Phosphoric bronze Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-1.0-2PLT-X	1.00	4.30	2.60
3	HC-1.0-3PLT-X	2.00	5.30	3.60
4	HC-1.0-4PLT-X	3.00	6.30	4.60
5	HC-1.0-5PLT-X	4.00	7.30	5.60
6	HC-1.0-6PLT-X	5.00	8.30	6.60
7	HC-1.0-7PLT-X	6.00	9.30	7.60
8	HC-1.0-8PLT-X	7.00	10.30	8.60
9	HC-1.0-9PLT-X	8.00	11.30	9.60
10	HC-1.0-10PLT-X	9.00	12.30	10.60
11	HC-1.0-11PLT-X	10.00	13.30	11.60
12	HC-1.0-12PLT-X	11.00	14.30	12.60
13	HC-1.0-13PLT-X	12.00	15.30	13.60
14	HC-1.0-14PLT-X	13.00	16.30	14.60
15	HC-1.0-15PLT-X	14.00	17.30	15.60
16	HC-1.0-16PLT-X	15.00	18.30	16.60

Ordering Information

HC-1.0 - N*** - *

Pin: 1.0mm
Type: 1.0mm
Colour: 1.0mm
Material: 1.0mm
Finish: 1.0mm

		GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
		DIM TOL	审核 CHECK				
		X.X ±0.30	批准 APPROVAL	产品名称 TITLE	1.0 立贴	版本 REV.	A
		X.XX ±0.20	比例 SCALE	产品料号 PART NO.	HC-1.0-NPLT-X	单位 UNITS	mm
1	初版发行		投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE					