



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >
Receptacle and Tab Housing: 2.5 mm Pitch, 250V



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **16**

Centerline (Pitch): **2.5 mm [.098 in]**

[All Receptacle and Tab Housing: 2.5 mm Pitch, 250V \(59\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	16
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Termination Features

--	--



Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	2.5 mm[.098 in]
--------------------	-----------------

Dimensions

Row-to-Row Spacing	3.3 mm[.129 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # CAT-D9934-A15F
Header Assembly: Wire-to-Board, 5A, gold or tin plated

Also in the Series

Dynamic 1000 Series

Connector Contacts(40)

Connector Hardware(3)

Insertion & Extraction Tools(2)

PCB Headers & Receptacles(173)

Rectangular Connector Housings(2)

Standard Rectangular Connectors(1)

Wire-to-Board Connector Assemblies & Housings(157)

Customers Also Bought

TE Part #2-1827864-2
Receptacle and Tab Housing: 2.5 mm Pitch, 250V

TE Part #917484-2
DYNAMIC D-3 REC CONT. 2L AU 0.38

TE Part #179955-2
DYNAMIC D-5 REC CONT. S FORM.

TE Part #1318105-1
DYNAMIC D-2000 REC CONT M



TE Part #1-1827579-1

DYNAMIC 1500T REC HSG 3P X BLACK

TE Part #62221-1

187 FASTON TAB TPBR

TE Part #2-1827875-8

DYNAMIC 1200D HDR ASSY V 16PY BLACK GOLD

TE Part #2294415-1

INDUSTRIAL MINI I/O HDR TYPE I TRAY

TE Part #4-2271099-0

CELLO,MALE,RA, 2.54PITCH, DIP3.0, WC

Documents

Product Drawings

DYNAMIC 1200D REC HSG 16PX BLACK

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1827864-8_P.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1827864-8_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1827864-8_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH

Japanese

1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH

English

Product Specifications

Application Specification

English



Instruction Sheets

Instruction Sheet (non U.S.)

English

Agency Approvals

TUV Certificate

English