



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Strain Relief Adapter**

Primary Product Material: **Nylon**

Primary Product Color: **White**

UL Flammability Rating: **UL 94V-0**

Packaging Method: **Bag**

Features

Product Type Features

|                              |                       |
|------------------------------|-----------------------|
| Strain Relief Accessory Type | Strain Relief Adapter |
|------------------------------|-----------------------|

Body Features

|                          |       |
|--------------------------|-------|
| Primary Product Material | Nylon |
| Primary Product Color    | White |

Industry Standards

|                                           |              |
|-------------------------------------------|--------------|
| Compatible With Agency/Standards Products | CSA, UL, VDE |
| UL Flammability Rating                    | UL 94V-0     |

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Method   | Bag  |
| Packaging Quantity | 6000 |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                              |           |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|



|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 641777-1  
UMNL STR/REL ADAPTER NATL



TE Part # 643182-1  
UMNL STR/REL ADAPTER CAP NATL



TE Part # 641778-1  
UMNL STR/REL ADAPTER



TE Part # 641778-2  
UMNL STR/REL ADAPTER \*NO NIBS\*



TE Part # 350848-5  
05P UMNL PLUG TEST ASSY 94V0



TE Part # 641777-2  
UMNL STR/REL ADAPTER \*NO NIBS\*



TE Part # 643131-2  
UMNL STR/REL ADAPTER CAP

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Caps & Covers(34)



Connector Contacts(209)



Connector Hardware(12)



Connector Seals & Cavity Plugs(27)



Connector Strain Relief(7)



Insertion & Extraction Tools(4)



Rectangular Connector Housings(1)



Rectangular Power Connectors(672)

Customers Also Bought



TE Part #745205-7  
15 HDE AP RECEPT, LEAD FREE



TE Part #641776-1  
04P UMNL STR/REL



TE Part #640714-1  
03P UMNL STR/REL



TE Part #350778-1  
02P UMNL CAP HSG




TE Part #1-640719-0  
02P UMNL STR/REL & INSRT NATL



TE Part #1445048-6  
PANEL MT SNGL ROW HSG 6 POS



TE Part #MTRA61274CB2-001  
OMNI,DB,Ph,617/1690 MHz



TE Part #8N1517-32-25P  
REC, 32P, AL, N, 4/8/12/16, P





Documents

Product Drawings

UMNL STR/REL ADAPTER CAP

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_643182-2\_R.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_643182-2\_R.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_643182-2\_R.3d\_stp.zip

English

3D PDF

English

Customer View Model

ENG\_CVM\_643182-2\_C.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_643182-2\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_643182-2\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT\_SHELL\_PIN\_SOCKET\_CONNECTORS\_STANDARD\_DENSITY

English

Product Specifications

Application Specification

English



Instruction Sheets

Instruction Sheet (U.S.)

English