









HRS No.	Number of Contacts	D	E	F	G	H
CL686-0055-0-52	10	16	—	7.5	7.6	16.4
CL686-0056-0-52	20	24	—	11.5	12.6	24.4
CL686-0057-0-52	30	32	28.4	14.2	17.6	32.4
CL686-0058-0-52	40	44	40.4	20.2	22.6	44.4
CL686-0053-0-52	50	44	40.4	20.2	27.6	44.4



HRS		 Made In China
品名コード(CI code) CL686-00**-0 52		
HRS品名 DF20EF-*DP-1V(52)		
数量 1RL(1000pcs)		
トレースNo. *****-*****-*****		

- Notes
- 1 reel 1000 connectors.
 5. At the beginning of the reel, 30 boxes shall be empty.
At the end of the reel, 20 boxes shall be empty.
 6. When the tape width is 16 or 24mm, sprocket holes shall be only set on the upper side of reel.
 7. Refer to 'Mating/Unmating Operation Manual' (ETAD-H0997-00) when operating this connector.

HRS	DRAWING NO.	EDC-391810-52-00	
	PART NO.	DF20EF- *DP-1V(52)	
	CODE NO.	CL686-	 