




Connectors > Contacts > Connector Contacts > Contact: Component To Wire; 15A, 28-14 wire size



Contact Type: **Tab**

Contact Mating Area Plating Material: **Gold**

Wire Size: **.08 – .24 mm²**

Product Terminates To: **Wire & Cable**

All Contact: **Component To Wire; 15A, 28-14 wire size (91)**

Features

Contact Features

Mating Tab Width	2 mm[.08 in]
Mating Tab Thickness	.64 mm[.025 in]
Contact Type	Tab
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	15 A

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Dimensions

Wire Size	.08 – .24 mm ²
-----------	---------------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------



Packaging Features

Packaging Method	Reel & Box
------------------	------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-D9934-A75B
Receptacle and Tab Housing: 5.08 mm Pitch, 250-600V

TE Part # CAT-D9934-A75C
Receptacle and Tab Housing: 5.08 mm pitch, 600V

TE Part # CAT-D9934-A75A
Receptacle and Tab Housing: 3.81 mm pitch, 250V

TE Part # 234168-1
EXTRACTION TOOL(DYNAMIC D-3)





TE Part # 91565-1
CCII D-3 S REC TAB 28-24 ASSY



TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # 2381453-1
SDE F DYNAMIC D3000 28-24AWG ASSY



TE Part # 2381453-2
SDE F DYNAMIC D3000 28-24AWG DIE SET



TE Part # 2836130-1
OCEAN_2.0_APPLICATOR-S-055F080F



TE Part # 2836130-2
OCEAN_2.0_APPLICATOR-S-055F080FA



TE Part # 7-2836130-1
OCEAN_2.0_APPLICATOR-S-055F080F



TE Part # 7-2836130-2
OCEAN_2.0_APPLICATOR-S-055F080FA



TE Part # 7-2836130-7
OCEAN_2.0_SPARE_PART_KIT-055F080F

Also in the Series | Dynamic 3000 Series




Connector Contacts(94)




Connector Hardware(8)



Insertion & Extraction Tools(2)



PCB Headers & Receptacles(283)



PCB Terminal Blocks(25)



Standard Rectangular Connectors(2)



Wire-to-Board Connector Assemblies & Housings(152)

Customers Also Bought



TE Part #1-1903131-3
DYNAMIC 1200D TAB HSG 6P P/M

TE Part #1-178129-6
DYNAMIC 3200 REC HSG 6P (DBL)

TE Part #1318110-1
DYNAMIC D-2000 TAB CONT S

TE Part #6-104693-0
100 50/50HDR DRST SFMNT.390 SN

TE Part #1-163081-1
.062 DIA PIN ASSY 3+

TE Part #1318095-1
DYNAMIC D-3500 REC HSG 6P

TE Part #4-456135-4
CRIMPER INSUL O

TE Part #1333202-2
ANVIL, COMBINATION .062

TE Part #2834207-1
2.5MM LATCH LOCK PLUG CONTACT

Documents

Product Drawings

DYNAMIC D-3 TAB CONT. S AU 0.38

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_175284-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_175284-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_175284-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH

Japanese

1-1773732-4_DYNAMIC_SERIES_CATALOG_ENGLISH

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

MULTIPLE ENCLOSURE 67M D1200 15POS. TAB PLUG

Japanese

Instruction Sheet (non U.S.)

Japanese

Agency Approvals

TUV Certificate

English