



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 4-1579007-3
EXTRACTION TOOL KIT



TE Part # 1-1579007-6
EXTRACTION TOOL



TE Part # 58603-2
PROCrimp DIE JPT 2.8MM TAB



TE Part # 2063490-1
SDE TAB 0.5-2.5mm2 ASSY



TE Part # 2063490-2
SDE TAB 0.5-2.5mm2 DIE SET


Customers Also Bought



TE Part #1-967626-1
AMP MCP Unsealed Connector Housings




TE Part #962880-1
TIMER, RECEPTACLE AND TAB




TE Part #1062-14-1088
SOC, SF, SIZE 16, 14-18, PD/NI/AU



TE Part #1-968875-1
AMP MCP 2.8, CONTACT SWS (LP)



TE Part #1-968873-1
AMP MCP 2.8, CONTACT (LP)



TE Part #1-963745-1
SPECIAL TERMINAL 20-17 AWG PTPB LP

Documents

Product Drawings

SPECIAL TERMINAL 17-13 AWG PTPB LP

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-963746-1_O.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1-963746-1_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-963746-1_O.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English