


Specification Sheet

Part Number: 170-23000



Nylon monofilament construction weave offers a tight braid that provides full coverage but will not rot or retain moisture. Material performs well in wet applications and where abiding substrate has a smooth surface.

Helagaine Braided Sleeving, 30 mm Dia, PA66, GY, 164ft/Reel

Article Number	170-23000
Type	HEGPA6630
Color	Gray (GY)
Quantity Per	metre
Product Description	Helagaine Nylon Polyamide Expandable Braided Sleeving is a pliable yet durable sleeve that protects against cuts, abrasion and excessive wear caused by repetitive motion.
Short Description	Helagaine Braided Sleeving, 30 mm Dia, PA66, GY, 164ft/Reel
Global Part Name	HEGPA6630-PA66-GY

Length L (Imperial)	164.0
Length L (Metric)	50.0
Bundle Diameter Min (Imperial)	0.98
Bundle Diameter Min (Metric)	25
Bundle Diameter Max (Imperial)	1.26
Bundle Diameter Max (Metric)	32
Diameter D (Imperial)	1.18
Diameter D (Metric)	29.9
Nominal Diameter (Imperial)	1.25
Nominal Diameter (Metric)	30
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2 FMVSS 302
Halogen Free	Yes
UV Resistant (Yes/No)	No

Operating Temperature	-76°F to +302°F (-60°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	164.0
Package Quantity (Metric)	50
Customs Number	5808100000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)