



NOTES:

- 1.CIRCUIT: ON/OFF
- 2.RATING: 16A 125/250VAC 3/4HP 125/250VAC(CUL)
16(4)A 125/250V~ T125/55 5E4 (ENEC17;NEMKO;CB)
16(4)A 250~ T125/55 1E4 (CQC)
- 3.CONTACT RESISTANCE: <50MΩ
- 4.INSULATION RESISTANCE: >100MΩ(500VDC BETWEEN OPEN CONTACTS)
- 5.DIELECTRIC STRENGTH: >1500VAC 0.5MA 1 MINTUTE
- 6.ACTUATOR COLOR:WHITE
HOUSING COLOR:WHITE
BASE COLOR:BLACK
- 7.ALL MATERIALS ARE ROHS COMPLIANT







TEL: 0769-82310511-867

WHEN THE SWITCH IS ON THE "ON" STATE,
DIMENSION A IS 3.0 mm, AND THE "OFF"
STATE, DIMENSION A IS 6.0 mm

PANEL CUTOUT DIMENSION:



PCB LAYOUT



NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM	DRAWING NO.	REV.
1		6		X.XX	±0.10				LMC	SCALE	NO		
2		7		X.X	±0.20				2022.02.15	MAT'L	***		
3		8		X	±0.30					MATERIAL NO.			
4		9		RANGE	TOLERANCE								
5		10		DIMENSIONAL TOLERANCES									
						LEGION ELECTRONIC & HARDWARE CO., LTD.					MPS21-WWBCG-R		
											WIF321001 A0		