



4 3 2 1






NOTES:

- 1.Rating : 16A GP 125/250VAC 5E4 40T125
16(4)A 125/250VAC 5E4 40T125
16A 42VDC 5E4 40T125
- 2.Contact resistance : 50mΩ Max
- 3.Insulation resistance : >100MΩ (Min) 500VDC
- 4.Dielectric strength : >1500VAC 0.5mA 1 minutes
- 5.Silver contact : Gold-plated
- 6.Low current range: 0~0.5A

TEL:0769-82310510-867

legion 六鈞電子



⑤	→	⑩	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN LMC 2021.02.26	ALL SIZE ARE IN	MM			
④	→	⑨	→	RANGE	TOLERANCE					SCALE	NO			
③	→	⑧	→	X	±0.30					MAT'L	***			
②	→	⑦	→	X.X	±0.20					MATERIAL NO.			DRAWING NO.	REV.
①	→	⑥	→	X.XX	±0.10					RT-M1-10C5J16C050-B			WIF122025	AO
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.								

4 3 2 1