



PANEL CUT-OUT

NOTES:

1. Electrical rating : 10A 250VAC VDE
15A 250VAC UL CUL
2. Insulation resistance : >100MΩ Min 500VDC
3. Dielectric strength : >2000V 1 minute

TEL: 0769-82310511-867

3	2# pin	C2680 1/2H	Tin-plating 3~5um	1
2	1# pin	C2680 1/2H	Tin-plating 3~5um	2
1	BODY	PA66 UL94V-0	Black	1
NO.	PART NAME	MATERIAL		Q'TY

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM	
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO	
3	→	8	→	X	±0.30				2020.02.26	MAT'L	***	
2	→	7	→	X.X	±0.20					MATERIAL NO.	DRAWING NO.	
1	→	6	→	X.XX	±0.10					RT-C14-G00B-AA	*****	AO
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LECION ELECTRONIC & HARDWARE CO., LTD.						

