











NOTES:

- 1.Electrical rating : 10A 250VAC VDE CCC  
15A 250VAC UL CUL
- 2.Insulation resistance : >100MΩ Min 500VDC
- 3.Dielectric strength : >2000V 1 minute

TEL: 0769-82310511-867

|     |           |                    |                   |      |
|-----|-----------|--------------------|-------------------|------|
| 3   | 2# pin    | C2680 1/2H         | Tin-plating 3~5um | 2    |
| 2   | 1# pin    | C2680 1/2H         | Tin-plating 3~5um | 1    |
| 1   | BODY      | PA66 UL94V-0 Black |                   | 1    |
| NO. | PART NAME | MATERIAL           |                   | Q'TY |

|    |             |    |             |                        |           |                                      |         |        |            |                 |     |             |      |
|----|-------------|----|-------------|------------------------|-----------|--------------------------------------|---------|--------|------------|-----------------|-----|-------------|------|
| 5  | →           | 10 | →           | DIMENSIONAL TOLERANCES |           | APPROVED                             | CHECKED | DESIGN | DRAWN      | ALL SIZE ARE IN | MM  |             |      |
| 4  | →           | 9  | →           | RANGE                  | TOLERANCE |                                      |         |        | LMC        | SCALE           | FIT |             |      |
| 3  | →           | 8  | →           | X                      | ±0.3      |                                      |         |        | 2017.12.29 | MAT'L           | *** |             |      |
| 2  | →           | 7  | →           | X.X                    | ±0.2      |                                      |         |        |            | MATERIAL NO.    |     | DRAWING NO. | REV. |
| 1  | →           | 6  | →           | X.XX                   | ±0.1      |                                      |         |        |            | RT-C14-F0B-LL   |     | WIF118010   | AO   |
| NO | DESCRIPTION | NO | DESCRIPTION | ANGLES                 | ±1°       | LEGION ELECTRONIC & HARDWARE CO.,LTD |         |        |            |                 |     |             |      |