


REV.	DATE	DESCRIPTION
C	04/31/03	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex								
7						DRAWN	G.R.S.						04/31/03			
6						CHECKED										
5	GASKET	SILICONE	RED	1			ISSUED		PART DESCRIPTION							
4	RETAINER RING	BER. COPPER	NATURAL	1			SHEET	1 OF 1	SMA SEMI-RIGID PLUG (FOR .141” SEMI-RIGID CABLE)							
3	CONTACT PIN	BRASS	GOLD	1					PART NO.							
2	INSULATOR	TEFLON	NATURAL	1					132102							
1	SHELL/BODY	BRASS	GOLD	1												
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE		DWG. NO.	132102.DWG	REV.	C	SIZE	A	SCALE	NA
							C:/132/132102.DWG									