





1. 按键开关型号PUSH BUTTON SWITCH MODEL NO. MPS11-MS180-M-R
2. SOLDERING TYPE, SHORT TERMINAL
3. 额定值RATING: 16A 125VAC/10A 250VAC(C-UL)
TV-5(C-UL)
5A/80A 250V~ μ T85(ENEC17;NEMKO;CB)
12A 250VAC 5/80A 250V~ μ T125(CQC)
4. 操作方式OPERATION MODE: MOMENTARY(NON-LOCK)
5. 所有部件均使用环保材料
ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE

TEL: 0769-82310511-867



2.5±0.3 LOCK STROKE

3.5±0.3 FULL STROKE



				DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN LMC 2019.05.20	ALL SIZE ARE IN	MM		DRAWING NO.	REV.
				RANGE	TOLERANCE					SCALE	NO			
				X	±0.30					MAT'L	***			
				X.X	±0.20					MATERIAL NO.				
				X.XX	±0.10									
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.				MPS11-MS180-M-R	WIF119111	A		