

Remarks:


- 1、Do not cut off copper wire when cutting wire.
- 2、Do not burn wire when baking heat-shrink tube.
- 3、Pull-force of terminal should reach the standard.
- 4、Hook/clasp the wire and solder with terminal of socket.

Test condition


- 1.Short/open circuit: 100% test

TEL: 0769-82310511-867

序号	名称	数量	规格
1	AC插座	1	RT-C14-L00B-AA 10A/15A 250VAC
2	热缩套管	4	黑色热缩套管 L=15mm
3	线材	1	UL3385 18AWG 颜色: 棕色线
4	线材	1	UL3385 18AWG 颜色: 绿注黄条线
5	线材	1	UL3385 18AWG 颜色: 蓝色线
*C 6	热缩套管	1	黑色热缩套管 L=100mm
7	圆环端子	1	∅7.5*ID4.3*T0.4mm 镀锡端子
8	胶壳	1	3.96-3Y/8639-03 白色胶壳
9	端子	2	3.96-T/8478 镀锡端子



焊接(钩焊)示意图



Wiring table

P1	P2	P3
N Blue	1	
E Yellow/Green		RING TERMINAL
L Brown	3	

	→		→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		MM		
	→		→	RANGE	TOLERANCE					SCALE		NO		
	→		→	X	±0.30					MAT'L		***		
	→		→	X.X	±0.20					MATERIAL NO.		DRAWING NO.		REV.
	172 → 192 2022.02.14		→	X.XX	±0.10					RT-C14-L00B-AA-13		WIF121069		A1
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	ROCKTEK ELECTRICAL(SHENZHEN) CO.,LTD.								