










PANEL CUT-OUT



SECTION A-A



NOTES:

- 1.Electrical rating : 10A 250VAC VDE CCC
15A 250VAC UL CUL
- 2.Insulation resistance : >100MΩ Min 500VDC
- 3.Dielectric strength : >2000V 1 minute

TEL : 0769-82310511-867

3	2# pin	C2680 1/2H	Tin-plating 3~5um	2
2	1# pin	C2680 1/2H	Tin-plating 3~5um	1
1	BODY	PA66 UL94V-0 Black		1
NO.	PART NAME	MATERIAL		Q'TY

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	FIT		
3	→	8	→	X	±0.3				2018.07.07	MAT'L	***		
2	→	7	→	X.X	±0.2					MATERIAL NO.		DRAWING NO.	REV.
1	→	6	→	X.XX	±0.1					RT-C14-F0B-AA		*****	A
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	ROCK TEK ELECTRONIC(SHENZHEN) CO.,LTD.							