






1. 电路 CIRCUIT: ON-OFF-ON
2. 额定值 RATING: 10A 125/250VAC (C-UL)
12 (4)A 250V~T85/55 (ENEC17;NEMKO;CQC)
CUL APPROVAL FILE NO. E153399
ENEC17 CERTIFICATE NO. 3704
NEMKO CERTIFICATE NO. P15219978
CQC CERTIFICATE NO. CQC10002046596
CB CERTIFICATE NO. 87398
KC CERTIFICATE NO. SU02099-17001
3. 接触电阻 CONTACT RESISTANCE: <50mΩ
4. 绝缘电阻 INSULATION RESISTANCE: >100MΩ (500VDC BETWEEN OPEN CONTACTS)
5. 耐电压 DIELECTRIC STRENGTH: >1500VAC 0.5mA 1 MINUTE

TEL:0769-82310511-867



MOUNTING HOLE



t	X	Y
0.75~1.25	19.3 ^{+0.1} ₀	13.4 ^{+0.1} ₀
1.25~2.00	19.4 ^{+0.1} ₀	13.4 ^{+0.1} ₀

品 名	上盖/基座(颜色)
SS21-WWWBH-S6-R	白色/白色
SS21-BBWWH-S6-R	黑色/黑色
SS21-RBWWH-S6-R	红色/黑色

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2019.05.20	MAT'L	***		
2	→	7	→	X.X	±0.20					MATERIAL NO.			
1	→	6	→	X.XX	±0.10							DRAWING NO.	REV.
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.				SS21-**W*H-S6-R		WIF119057	A